

VESTAMID® *Care* ML



VESTAMID *Care* ML grades cover a range of polyamide 12 resins of different viscosity for processing via extrusion or injection molding. The VESTAMID *Care* ML product range consists of un-stabilized base resins as well as stabilized or reinforced compounds.

Flexible and reliable

VESTAMID® *Care* ML resins are characterized by several outstanding properties, such as high impact & notched impact resistance, dimensional stability, good sliding properties, high abrasion resistance and resistance against chemicals.

Unfilled VESTAMID® *Care* ML grades are for example the materials of choice for catheters and tubings, where VESTAMID® *Care* ML materials meet even highest challenges in applications such as angioplasty balloon catheters.

Typical areas of application for reinforced VESTAMID® *Care* ML grades include housing-parts, monitoring and imaging devices and durable medical equipment. Due to their low water uptake, filled VESTAMID® *Care* ML grades even resist steam autoclaving for more than 500 cycles.

The advantages at a glance

- High impact resistance
- High dimensional stability
- High chemical resistance
- Low sliding friction
- High toughness
- High abrasion resistance
- Easy processability & colorability

Approvals

VESTAMID® *Care* ML grades were tested on biocompatibility for applications within the body of up to 30 days contact time and comply with USP <88> class VI and ISO 10993 standards.

VESTAMID® Care ML – base resins

Properties	Test method int.	Unit	VESTAMID® Care ML16	VESTAMID® Care ML17	VESTAMID® Care ML18	VESTAMID® Care ML19	VESTAMID® Care ML21							
Density	23°C	ISO 1183	g/cm ³	1.02	1.02	1.02	1.02	1.01						
Tensile test 23°	50 mm/min	ISO 527-1/-2												
Stress at yield									MPa	45	45	45	45	45
Strain at yield									%	5	5	5	5	5
Nominal strain at break									%	>50	>50	>50	>50	>50
Tensile modulus		ISO 527-1/-2	MPa	1400	1400	1400	1400	1400						
CHARPY impact strength		ISO 179/1eU												
23°C									kJ/m ²	N	N	N	N	N
-30°C									kJ/m ²	N	N	N	N	N
CHARPY notched impact strength		ISO 179/1eA												
23°C									kJ/m ²	5 C	6 C	6 C	7 C	32 C
-30°C									kJ/m ²	5 C	6 C	6 C	7 C	9 C
Melting range DSC, 2 nd heating		ISO 11357	°C	178	178	178	178	178						
Temperature of deflection under load		ISO 75-1/-2												
Method A	1.8 MPa								°C	50	50	50	50	50
Method B	0.45 MPa								°C	110	110	110	110	110
Vicat softening temperature		ISO 306												
Method A	10 N								°C	170	170	170	170	170
Method B	50 N								°C	140	140	140	140	140
Linear thermal expansion 23 -55 °C		ISO 11359	10 ⁻⁴ K ⁻¹	1.5	1.5	1.5	1.5	1.5						
Flammability acc. UL94		IEC 60695												
3.2 mm									HB	HB	HB	HB	HB	
1.6 mm									HB	HB	HB	HB	HB	
Mold shrinkage		determined on 2mm sheets with film gate at rim, mold temp. 80°C ISO 294-4												
in flow direction									%	0.95	0.68	0.85	0.78	0.70
in transverse direction									%	1.09	1.22	1.03	1.10	1.25
Water absorption		ISO 62												
23°C, saturation									%	1.5	1.5	1.5	1.5	1.6
23°C, 50% relative humidity									%	0.7	0.7	0.7	0.7	0.8
Viscosity number		ISO 307	ml/g	120	140	160	180	230						

N = No break, P = Partial break, C = Complete break, incl. hinge break, HB = Horizontal burning

VESTAMID® Care ML- compounds

Properties	Test method int.	Unit	VESTAMID® Care ML67	VESTAMID® Care ML94	VESTAMID® Care ML24	VESTAMID® Care ML-GB30	
Density	23°C	ISO 1183	g/cm ³	1.01	1.01	1.01	1.25
Tensile test	ISO 527-1 ISO 527-2						
Stress at yield		MPa	46	45	47	47	
Strain at yield		%	6	5	5	5	
Nominal strain at break		%	>50	>50	>50	>50	
Tensile modulus	ISO 527-1/-2	MPa	1400	1350	1400	2000	
CHARPY impact strength	ISO 179/1eU						
23°C		kJ/m ²	N	N	N	160 C	
-30°C		kJ/m ²	N	N	N	160 C	
CHARPY notched impact strength	ISO 179/1eA						
23°C		kJ/m ²	4 C	6 C	16 C	6 C	
-30°C		kJ/m ²	5 C	6 C	9 C	6 C	
Melting range DSC, 2 nd heating	ISO 11357	°C	178	178	178	178	
Temperature of deflection under load	ISO 75-1/-2						
Method A	1.8 MPa	°C	50	50	50	55	
Method B	0.45 MPa	°C	120	120	110	150	
Vicat softening temperature	ISO 306						
Method A	10 N	°C	170	170	170	150	
Method B	50 N	°C	140	140	140	155	
Linear thermal expansion 23 -55 °C	ISO 11359	10 ⁻⁴ K ⁻¹	1.5	1.5	1.4	1.3	
Flammability acc. UL94	IEC 60695						
3.2 mm			HB	HB	HB	HB	
1.6 mm			HB	HB	HB	HB	
Mold shrinkage	determined on 2mm sheets with film gate at rim, mold temp. 80°C ISO 294-4						
in flow direction		%	0.9	0.85	0.65	1.2	
in transverse direction		%	1.1	1.15	1.25	1.2	
Water absorption	ISO 62						
23°C,saturation		%	1.4	1.5	1.6	1.1	
23°C/50% relative humidity		%	0.7	0.8	0.7	0.5	

This information and all technical and other advice are based on Evonik's present knowledge and experience. However, Evonik assumes no liability for such information or advice, including the extent to which such information or advice may relate to third party intellectual property rights. Evonik reserves the right to make any changes to information or advice at any time, without prior or subsequent notice. Evonik disclaims all representations and warranties, whether express or implied, and shall have no liability for, merchantability of the product or its fitness for a particular purpose (even if Evonik is aware of such purpose), or otherwise. Evonik shall not be responsible for consequential, indirect or incidental damages (including loss of profits) of any kind. It is the customer's sole responsibility to arrange for inspection and testing of all products by qualified experts. Reference to trade names used by other companies is neither a recommendation, nor an endorsement of the corresponding product, and does not imply that similar products could not be used.

® = registered trademark

Evonik Industries AG

Paul-Baumann-Straße 1, 45772 Marl, Germany

Phone +49 2365 49-9227